

## Evapco Evaporative Condenser- 269 Ton

Mfg: Evapco

Model: LRW-68-4-2

Stock No. 2000.WYB2.

Serial No. M014878

Evapco Evaporative Condenser- 269 Ton. Model: LRW-68-4-2. S/N's: M014878. Refrigerant: R-22. Conditions: 78 °F web bulb, 40 °F suction, 105 °F condensing temperature. Airflow: 43,240 cfm. Pumping capacity: 405 gpm. Coil volume: 266 gal. Centrifugal fan diameter: 27 in. Coil Test Pressure: 400 PSIG. The LRW is a low noise, low height, forced draft centrifugal design unit. Standard construction features the patented, high efficiency Thermal-Pak coil with a type 304 stainless steel cold water basin and G-235 galvanized steel casing. Included are the zero-maintenance PVC spray distribution headers with ZM nozzles. Motorpump 57E Standard Fitted, 4X3 BN-CM Seal, 1750 RPM. US Motor, 2 hp, 1725 rpm, 208-230/460 V, amps, Hz, phase. Fan Motor, 30 hp, 1765 rpm, 208-230/460 V, 60 Hz, 3 phase. Inlets: (2) 8 bolts 4 in. dia. flanges, 7 in. dia. NPT (female). Outlets: (2) 8 bolts 4 in. dia. flanges, (1) 2 in. dia. NPT (male), (1) 3 in. dia. NPT (male), (1) 8 bolts 4-1/2 in. dia. flange. Overall dimensions: 16 ft. 3-3/4 in. L x 7 ft. 10 in. W x 8 ft. 2-1/2 in. H.



