

Dorr-Oliver Eimco / Shriver Filter Press 36 in.

Mfg: Dorr-Oliver Eimco / Shriver

Model:

Stock No.: 100.3R-2299.30

Serial No.: 25442

Dorr-Oliver Eimco / Shriver Filter Press. S/N: 25442. (20) end plates and (23) spacer plates, all 36 in. L x 36 in. W. Maximum filtering pressure: 100 lbs. Power Team 2-Speed Manually-Operated Hydraulic Pump, Model: P460, S/N: 68907. Inlets: (1) 3 in. dia. I-Line (female). Outlets: (22) 1/2 in. dia. ports. Overall dimensions: 10 ft. 9 in. L x 4 ft. 4 in. W x 5 ft. 9 in. H.





