

1999 Dunham-Bush Air Cooled Chiller



Mfg: Dunham-Bush


Model: ACDX420B

Stock No.: DPLS224.43a

Serial No.: 12329701A99G

1999 Dunham-Bush Air Cooled Chiller. Model ACDX420B. S/N 12329701A99G. Refrigerated System. 460/3/60 Electrics, R-22 refrigerant, 1117# Charge. Compressor motor model numbers. 1215 NHF6X6K & 1218NHF6X6K. Compressor run times: no.1: 27690 hours, no. 2: 18234 hours, no. 3: 8608 hours.





MUST USE 2 1/2" NOMINAL PIPE THRU UNIT FOR SLINGS TO AVOID BASE DAMAGE.

MUST CLEAR TOP OF UNIT

017400A1

MODEL	AC0X4208	SER.	1331000000
PATENT		APPLICATION	
TEST PRESSURE, HIGH SIDE		PSIG	LOW SIDE
UNIT VOLTS / PH / HZ	480 / 3 / 60		PSIG
CNT VOLTS / PH / HZ	115 / 1 / 60		FACTORY ORDER
REF.	000	FIELD CHARGE	CONTROL AMPS
		LB	FACTORY CHARGE
			LB
		MODEL/HP	RLA/EA. LRA/EA. VOLTS/PH/HZ
COMPR MOTOR(S)	<input checked="" type="checkbox"/> NO/UNIT		
COMPR MOTOR(S)	<input checked="" type="checkbox"/> NO/UNIT		
CONDENSER FAN MOTOR(S)	<input checked="" type="checkbox"/> NO/UNIT		
CONDENSER FAN MOTOR(S)	<input checked="" type="checkbox"/> NO/UNIT		

007430A1-B

017400A1

MODEL		SER.	
TEST PRESSURE, HIGH SIDE		PSIG	APPLICATION
UNIT VOLTS / PH / HZ			LOW SIDE
CNT VOLTS / PH / HZ			PSIG
REF.		FIELD CHARGE	CONTROL AMPS
		LB	FACTORY CHARGE
			LB
COMPR MOTOR(S)	<input type="checkbox"/> NO/UNIT	MODEL/HP	RLA/EA. LRA/EA. VOLTS/PH/HZ
COMPR MOTOR(S)	<input type="checkbox"/> NO/UNIT		
CONDENSER FAN MOTOR(S)	<input type="checkbox"/> NO/UNIT	HP/W	FLA/EA. VOLTS/PH/HZ
CONDENSER FAN MOTOR(S)	<input type="checkbox"/> NO/UNIT		
CRANKCASE HEATER	<input type="checkbox"/> NO/UNIT		
CHILLER HEATER	<input type="checkbox"/> NO/UNIT		
	<input type="checkbox"/> NO/UNIT		
	<input type="checkbox"/> NO/UNIT		
MIN. CIRCUIT AMPACITY	CIRCUIT 1	CIRCUIT 2	
MAX. FUSE SIZE	CIRCUIT 1	CIRCUIT 2	PSI
REMOTE CONDENSER MINIMUM TEST PRESSURE			

007430A1-B

HARRISONBURG, VIRGINIA 22801 U.S.A.