



NOTES:

- ϵ 3/4 MOUNTING HOLES
- ⊙ 2 M.P.T. MAKE - UP (WATER PRESSURE 20psi MIN, 60psi MAX.)
- ▲ 3 F.P.T. OVERFLOW AND 3 M.P.T. DRAIN
- Ⓜ FAN MOTOR
- * APPROX. DIM. - DO NOT USE FOR PREFABRICATION OF CONNECTING PIPING
- VIEW B-B SAME AS A-A LESS MAKE-UP AND DRAIN CONNECTIONS, AND OPPOSITE HAND

VIEW A-A

UNIT NO.	H	C	R
PMC- 650N	13' 9-1/2"	59-1/2"	37-1/2"

APPROX. WEIGHT	
SHIPPING	OPERATING
34,380	37,140



evaporative condenser

REV:
DATE: 5/28/86

CERTIFIED FOR: _____
 CUSTOMERS ORDER NO: 2649 EVAPCO NO: 868021
 CAPACITY: 462 T.R. NH3 REFRIG 96.3° COND 20° SUCT 78° W.B.
 FAN MOTOR (2) 2sp/1 wind 10 H.P. ELEC. SPEC. 230 / 60 / 3
 PUMP MOTOR (2) 3 H.P. ELEC. SPEC. 230-460 / 60 / 3
 REMARKS To include (2) 10 KW pan heaters, 230/60/3, with thermostat and low water cutoff.
 Drives sized for 0" ESP.