

Copeland Air Cooled Condensing Unit

Mfg: Copeland

Model: F3AD-A201-CFV-001

Stock No.: ACEU1004

Serial No.:

Copeland Air Cooled Condensing Unit . Model: F3AD-A201-CFV-001. Maximum designed pressure, high side: 440 psig, low side: 162 psig. Copeland Scroll Compressor. Model: CRD1-0200-PFV-272. S/N: 00EH6406H. Capacity: 16,200 BTU. Power rating: 200-230 V, LRA: 57, 60 Hz, single phase. Refrigerant: R-22, R-502. (2) 1 ft. dia. fans with motors. Evaporator, 11 fins per inch, dimensions: 2 ft. 10 in. L x 6-1/2 in. W x 1 ft. 7 in. H. Shelby Manufacturer Co. Oil Separator-1.3 Gallon. Straight-wall dimensions: 6 in. dia. x 11 in. H. Inlet: (1) 3/4 in. dia. suction port. Outlet: (1) 1/2 in. dia. discharge port. Overall dimensions: 2 ft. 10 in. L x 2 ft. 1 in. W x 1 ft. 7 in. H.(ACN12).





