

## Bryant Carrier Air Cooled Condensing Unit- 30 Ton

Mfg: Bryant

Model: 576HPX3-0000AAAA

Stock No. ACEU53.

Serial No. 0397F48670

Bryant Carrier Air Cooled Condensing Unit- 30 Ton. Model: 576HPX3-0000AAAA. S/N: 0397F48670. Factory charged refrigerant: R-22. (2) Carlyle 6-Cylinder Semi-Hermetic Reciprocating Compressors. Compressor #1: Model 06DA3280DC3200, S/N: 4996J01179. 10 hp, 28 cfm @ 1,750 rpm, 208/230 V, min/max 187/254 V, LRA 228.0, RLA 43.6, 3 phase. Compressor #2: 06DA5370DC1200, S/N: 4696J02808. 15 hp, 37.1 cfm @ 1,750 rpm, 208/230 V, min/max 187/254 V, LRA 266.0, RLA 63.6 60 Hz, 3 phase. Design/test pressure high/low: 480/235 psig (3310/1620 kPa). Min. ckt amps: 135.5. Max overcurrent protection device amps: 175. Fans: (2) 30 in. dia. Magnetek Fan Motor: 1,140 rpm, 208-230/460-575 V, 5.5/2.8-3.4 amps, 60 Hz, 3 phase. General Electric Fan Motor: 1 hp, 1,140 rpm, 208-230/460 V, 6.50-5.50/3.30 amps, 60 Hz, 3 phase. Overall dimensions: 128 in. L x 68-1/2 in. W x 56 in. H.



