

Un-used Thermal Care/Mayer Air-Cooled Accuchiller- 3 Ton

Mfg: Thermal Care/Mayer

Model: AQOA0304X

Stock No. AFBC001.2a

Serial No. CH-04483

Un-used Thermal Care/Mayer Air-Cooled Accuchiller- 3 Ton. Model: AQ0A0304X. S/N: CH-04483. Accuchiller series AQ are built for quiet performance, nonferrous construction. Min/max temperature: 30/60 °F. 1% Capacity reduction per degree operated above 95 °F. Maximum ambient temperature: 110 °F. Evaporative range: 20 to 55. Scroll compressor, Model: AH302TT-195. 31 in. L x 2-1/2 in. W x 18 in. H condenser unit with 11 fins per inch. (2) condenser fan motors, 1/16 hp. Thermal Care/Mayer Motorpump with Magnetek Motor, 3/4 hp, 3450 & 2850 rpm, 200-230/460 V, 60 & 50 Hz, 3.8-3.6/1.8 SF, 3 phase. Impeller diameter: 3.88 in. diameter. Microprocessor controller provides diagnostics, easy operation and accurate temperature control. (4) Casters for easy positioning. Inlets: 1-1/4 in. NPT (female). Outlets: (1) 1-1/4 in. NPT (female). Overall dimensions: 80 in. L x 34 in. W x 55 in. H.





