

Frick Rotary Screw Compressor Unit

Mfg: Frick


Model: RWB100

Stock No. ASLC012.

Serial No. SO744NFMCTHAA3

Frick Rotary Screw Compressor Unit. Model RWB100. S/N SO744NFMCTHAA3. Frick Sales Order 209503-09. Refrigerant R-717, max speed 3600 rpm. Rotary Screw Compressor. Model/Serial No. TDSH193S2036C. Refrigerant NH3/R22, vol ratio 2.2 : 5.0, max speed 3600 rpm, max design pressure 362 psig. 250 hp, 460 V, 3 phase, 60 hz, fla 294. Hours 42,931.





Job NO: SOP 3014235		
Drawing No.: FKC-4256Y1033		
Volts: 460	Phase: 3	Hz: 60
H.P.: 250	FLA: 294	LRA:
LARGEST H.P.: 2.50		

OCT 20 2006

