

Frick Rotary Screw Compressor Unit

Mfg: Frick

Model: RXF24

Stock No. ASLC015.

Serial No. SO044MFMNLHAA2

Frick Rotary Screw Compressor Unit. Model RXF24. S/N SO044MFMNLHAA2. Frick Sales Order 209079-01. Refrigerant R-717, max speed 1800 rpm, max design pressure 300 psi. Rotary Screw Compressor. Model/Serial No. XJF120S0182DD. Refrigerant NH3/R22, vol ratio 2.2 : 5.0, max speed 3600 rpm, max design pressure 362 psig. 70 hp, 460 V, 3 phase, 60 hz, fla 99.3. Hours 97,114.



Job NO:	SOP 3013853				
Drawing No.:	FKC-475F/03				
Volts:	460	Phase:	3	Hz:	60
H.P.:	75	FLA:	99.3	LRA:	
LARGEST H.P.:	75				



