

1995 Cherry Burrell Jacketed Processor Tank-1,000 Gallon

Mfg: Cherry Burrell

Model:

Stock No. ATE204.

Serial No. F-010-95

1995 Cherry Burrell Jacketed Processor Tank-1,000 Gallon. 316 Stainless Steel. S/N: F-010-95. MAWP @ 350 °F: 100 psi . MDMT@ -20 °F: 100 psi. Tank features internal agitation produced by (4) agitator blades and external heating via (6) heat zone steam headers. Simens Motor, 2.0 hp, 1,735 rpm, 230/460 V, 6.2/3.1 amps, 60 Hz, 3 phase. NORD Motor Drive, 52.03 ratio, 33 rpm (final), 2945 in-lbs torque. Inlets: (2) 1 in. dia. thermowells, (1) 1-1/2 in. dia. NPT (female bevel), (1) 1-1/2 in. dia. NPT (male bevel), (2) 2 in. dia. S-line fittings, (2) 2-1/2 in. dia. S-line fittings, (2) 4 in. dia. S-line fittings. Outlets: (2) 1-1/2 in. dia. NPT ball valves, (1) 2 in. dia. pneumatic valve, (1) 2-1/2 in. dia. S-line fitting (tank). Overall dimension: 90 in L x 90 in. W x 140 in. H.





