

Baltimore Air Coil Evaporative Condenser- 300 Ton

Mfg: Baltimore Air Coil

Model: VXMC-300

Stock No. BAOT165.

Serial No. 81-9244

Baltimore Air Coil Evaporative Condenser- 300 Ton. Model: VXMC-300. SN: 81-9244. Belt No: 13-144. Refrigerants: R-22 or Ammonia. Nominal tonnage is based on 105 °F condensing temperature, a 40 °F suction temperature, and a 78 °F wet-bulb temperature. Unit contains (2) blower fans with 10 hp U.S. Motors and a Paco centrifugal pump. Inlets/outlets: (4) 4 in. dia. valves. Overall dimensions: 13 ft. 9 in. L x 9 ft.11 in. W x 12 ft. 11 in. H.

Paco Centrifugal Pump, Model: I0-30501-710061-1681, S/N: 60062017 30 -206, capacity: 490 gpm, TDH: 15 ft., impeller diameter: 4.50 in. Motor, 5 hp, 3,510 rpm, 230/460 V, 14.2 / 7.1 amps, 60 Hz, 3 phase. U.S. Fan Motor, 10 hp, 3,755 rpm, 230/460 V, 26/12 amps, 60 Hz, 3 phase.



