

**1991 Morris & Associates Ice-Master® Remote Ammonia Nugget Ice Maker**

**Mfg: Morris & Associates**

**Model: NIM-RA-40LR**

**Stock No. BBCF161.130**

**Serial No. 384-1091**

Stainless Steel Ice Bin.

Stainless Steel Screw Auger. Screw auger dimensions: 8 in. dia. x 5 ft. L. Overall dimensions: 5 ft. 7 in. L x 10 in. W x 8 in. H.

Stainless Steel Covers. Overall dimensions: 3 ft. 4 in. L x 7 ft. 6 in. H.

Stainless Steel Base Plates (thin gage): 5 ft. L x 3 ft. W x 3 ft. H.

Stainless Steel Base Plates (thick gage): 4 ft. 1 in. L x 3 ft. 8 in. W x 4 ft. ½ in. H.

LD Industries Rotating Assembly. Model: 280. S/N: 392001. Job No: 20139. Lincoln AC Motor, 7.5 hp, 1745 rpm, 230/460 V, 20.4/10.2 amps, 60 Hz, 3 phase. Overall dimensions: 5 ft. 4 in. L x 5 ft. 2 in. W x 4 ft. H.

(3) 1994 Global Manufacturing Air Blaster Tanks- 10 Gallon. S/Ns: 88074, 88075, and 88091. Inside straight-wall dimensions: 10 in. dia. x 2 ft. 10 in. L. MAWP: 150 psi @ 450°F. MDMT: -20°F @ 150 psi. Overall dimensions: 3 ft. 9 in. L x 1 ft. 7 in. W x 1 ft. 6 in. H.

(21) Leg supports. Overall dimensions: 3 ft. 6 in. L x 8 in. W x 4 in. H.





COMPRESSED AIR INLET  
80-125 P.S.I.

USE FILTER, REGULATOR AND ONE-WAY  
CHECK VALVE ON INPUT LINE.

USE 3-WAY, 2-POSITION, NORMALLY-OPEN  
VALVE TO CONTROL AIR BLASTER. DO NOT  
RESTRICT EXHAUST AIR PORT OF VALVE.



