

## Frick RXB 39H Rotary Screw Compressor Package - 75 HP

Mfg: Frick

Model: RXB 39H

Stock No: BDBS02

Serial No: S0008EFENWHAA3

Frick RXB 39H Rotary Screw Compressor Package. Model: RXB-39H. S/N: S0008EFENWHAA3. Frick order no: 261826-01. Refrigerant: Last used with R-717 (ammonia). Frick rotary screw compressor. Model/Serial: XJS120L0037FR. Vi setting: 2.2 to 5.0. Displacement: 222 cfm. Max speed rpm: 3600. Max design pressure: psig: 350. Frick oil separator. SN: 68162. National Board: 68182. MAWP: 300 psi at 200°F. Radius: 2:1 elliptical ends. Frick oil cooler. National Board: 68868. MAWP: 300 psig at 200°F. MDMT: -20°F at 350 psig. Frick oil filter housing. S/N: MC87030. MAWP: 350 psig at 200°F. MDMT: -20°F at 350 psi. Marathon Electric motor, 75hp, 3550 rpm, 92 amps, 460 V, 60 Hz, 3 phase. Frick RXB electromechanical control panel. Inlets: (1) 3 in. dia. suction port. Outlets: (1) 2-1/2 in. dia. discharge port. Compressor run time: 18,804 hrs. Overall dimensions: 8 ft. L x 4 ft. 9 in. W x 6 ft. 8 in. H.









