

Evapco Evaporative Condenser - 175 Tons


Mfg: Evapco

Model: PMCB-175

Stock No: BDBS06

Serial No: T020521

Evapco Evaporative Condenser. Model: PMCB-175. S/N: T020521. Belt No: 2B-116. Nominal rated capacity: 175 tons using R-22 at 105°F condensing, 40°F suction and 78°F wet bulb temperatures. 125 tons using R-717 at 96.3°F condensing, 20°F suction and 78°F wet bulb temperatures. Coil test pressure: 400 psig. Forced draft design with axial fans. Number of axial fans: 2. Fan diameter: 3 ft. 8 in. Fan motor: 7.5 hp, 1760 rpm, 460 V, 60 Hz, 3 Phase. Pump: 5.25 impeller diameter, 2 hp, 1750 rpm, 3/60/200-230/460V. Motor: 2.0 hp, 1725 rpm, 208-230/460V, 71/3.6 amps, 60 Hz, 3 Phase. Inlet: (1) 2 in. dia. port, (2) 4 in. dia. port. (2) 1 ft. 8 in dia. port, (2) ¾ in. dia. port. Outlet: (2) 2 in. dia. port. (2) 4 in. Approximate shipping weight 3560 lbs. Overall dimensions: 13 ft. 5 in. L x 6 ft. 5 in. W x 11 ft. 1 in. H. (ACN271).





evapco

EVAPCO, INC.
5151 Allendale Lane Taneytown, MD. 21787
(410) 756-2600 Fax # (410) 756-6450
MFG. UNDER ONE OR MORE OF THE FOLLOWING U.S. PATENTS:
4500330, 4579604, 4755331, 5124007

MODEL NO. F40CB-1/25	SERIAL NO. 7020921
BELT NO. 26-116	COIL TEST PRESSURE 400 P.S.I.G.

MADE IN U.S.A.

FOR EVAPCO AUTHORIZED PARTS AND SERVICE, CONTACT MR. GOODTOWER™

MIDATLANTIC REFRIGERATION, INC.
8400 Baltimore National Pike #284
Baltimore, MD 21228
Phone: (410) 247-1898
Fax: (410) 247-1897

