

## APV Gaulin Homogenizer

**Mfg: APV Gaulin**

**Model: 1057 M12 3TP SX**

**Stock No.: BIIR9001.80**

**Serial No.: 48610036**

APV Gaulin Homogenizer. Model: 1057 M12 3TP SX. S/N: 48610036. Maximum capacity: 1057 gph. 2-stage hydraulic valve assembly. 1-1/2 in. dia. plungers. Spring loaded poppet valve cylinders. Maximum cylinder design pressure: 3000 psig. Cylinder block S/N's: 04747,957693,15\*5 PH, 225312, ALTEC. Reliance Electric Motor, 40 hp, 1770 rpm, 200 V, 115 amps, 60 Hz, 3 phase, Driver pulley diameter: 9 in. Driven pulley diameter: 1 ft, ratio: 0.75, rpm out: 1327 (final). Hydraulic pump with Baldor Industrial Motor, 3/4 hp, 1725 rpm, 208-230/460 V, 3.2-3.0/1.5 amps, 60 Hz, 3 phase. Inlets: (1) 3/4 in. dia. S-line fittings. Outlets: (1) 1-1/4 in. dia. S-line fittings. Overall dimensions: 4 ft. L x 3 ft. 4 in. W x 3 ft. 11 in. H. Missing: (1) Oil Level Sight Glass. Needs: (all) Packing.(ACNXX-86)







