

Baltimore Air Coil Evaporative Condenser - 400 Tons

Mfg: Baltimore Air Coil

Model: VLC- 400

Stock No: BNCA173A

Serial No: 764067P

Baltimore Air Coil Company Evaporative Condenser. Model: VLC-400. S/N: 764067P. Nominal rated capacity: 400 tons using R-22 at 105°F condensing, 40°F suction, and 78°F wet bulb temperatures or 288 tons using R-717 at 96.3°F condensing, 20°F suction and 78°F wet bulb temperatures. Last used with ammonia. Belt No. B90. The fans, motor, and drive system are located outside of the moist discharge airstream, protecting them from moisture, condensation and icing. Unit is suitable for year-round operation. Number of fans: 8. Fan diameter: 1 ft. 7 in. Number of motors: 4. Typical motor, 7.5 hp, 1740 rpm, 230/460 V, 21.6/10.8 amps, 60 Hz, 3 phase. Inlets: (2) 3 in. dia. ports, (1) 4 in. dia. port. Outlets: (2) 2 ½ in. dia. ports, (1) 6 in. dia. port. Overall dimensions: 18 ft. 6 in. L x 9 ft. 1 in. W x 10 ft. 6 in. H.(ACN565)(BH).





