

Copeland Freon Compressor

Mfg: Copeland

Model: ARE25C3E-SAA-103

Stock No.: BZCH369.a

Serial No.: 04C93161E

Copeland Freon Compressor. Model: ARE25C3E-SAA-103. S/N: 04C93161E. Refrigerant: R134A (freon). Fan diameter: 8-1/2 in. Number of fans: 1. Power supply: 115 V, 25 amps, 60 Hz, single phase. Copeland condenser, Model: M2FH-0024-SAA-106. Max design pressure: 440 psig (hi) ,162 psig (low). Max evap. temperature: 45° F. Power supply: 115 V, 4.47 amps, 60 Hz, single phase. Inlets: (1) 1/4 in. dia. port. Outlets: (1) 1/4 in. dia. port. Overall dimensions: 1 ft. 2 in. L x 1 ft. 2 in. W x 10 in. H.





