

Frick Rotary Screw Compressor

Mfg: Frick

Model: TDSH193S1364C

Stock No. CFPH697.1

Serial No. TDSH193S1364C

Frick Rotary Screw Compressor. Model & S/N: TDSH193S1364C. Refrigerants: R-717 (ammonia), R-22 (Freon). Vol. ratio: 22-50. Maximum pressure: 362 psig. Max speed: 4500 rpm. Shaft diameter: 2-3/16 in. Overall dimensions: 5 ft. 2 ft. 5 in. W x 2 ft. 4 in. H.



