

Frick RWB Rotary Screw Compressor Package- 300 HP

Mfg: Frick

Model: 93

Stock No. CSRW003.

Serial No. 2018DLR3x4454

Frick RWB Rotary Screw Compressor Package- 300 HP. Model: 93. S/N: 2018DLR3x4454. Natd Bd: 44998. Refrigerant: R-717. Compressor run time: 22451 hrs. Volume ratio: 4.15. Max Speed: 3600 rpm. Maximum pressure: 300 psig. MAWP: 300 psig @ -20 to +200 °F. MDMT: -50 °F. Teco Motor, 300 hp, 3573 rpm, 327 amps, 460 V, 60 Hz, 3 phase. Viking Rotary Pump, Model: AK-190, S/N: Z2969. Leeson Motor, 5 hp, 1140 rpm, 230/460 V, 16/8 amps, 60 Hz, 3 phase. Inlets/outlets: (1) 5 in. dia., 8-bolt flanged port, (1) 4 in. dia. 4-bolt flanged port, (2) 1-1/2 in. dia. NPT (female) port. Over dimensions: 12 ft. L x 46 in. W x 97 in. H.



