

York Air Cooled Liquid Chiller- 100 Ton

Mfg: York

Model: YCAS08446

Stock No. CSSD201.7a

Serial No. YBWL101498

York Air Cooled Liquid Chiller- 100 Ton. Model: YCAS08746PA. S/N: YBWM179579. Refrigerant: R-22. Evap: 170 gpm @ EWT: 53 °F, LWT: 42 °F, AMB: 100. For outdoor use. Power supply: 460 V, 60 Hz, 3 phase. Control power supply: 115 V, 60 Hz, single phase. (2) Compressors- 50 HP, 80 RLA, 510 LRA. (2) Condenser fans- 5hp, 7.1 RLA, 41.8 LRA. (1) Cooler: 18 in. dia x 104 in. L. Overall dimensions: 115 in. L x 86 in. W x 88 in. H.

(2) Compressors, Mfg: Compressor Products Inc., Model: 8DP 5000 FSD, S/N: 11445 and 11437, 50 hp, 460 V, 60 Hz, 3 phase, 80 RLA, 510 LRA.

(2) Condensor fan motors: 5 hp, 460 V, 60 Hz, 3 phase, 7.1 FLA, 41.8 LRA.

(2) Oil heaters: 115 V, 60 Hz, 1 phase, 100 watts ea.

(1) Cooler: 18 in. dia x 104 in. L, 4 in. inlet, 4 in. outlet, (2) 3 in., (2) 2 in.

Overall dimensions: 115 in. L x 86 in. W x 88 in. H.



