

## York Air Cooled Liquid Chiller- 100 Ton

Mfg: York

Model: YCAS08446

Stock No. CSSD202.7a

Serial No. YBWL101498

York Air Cooled Liquid Chiller- 100 Ton. Model: YCAS08446. S/N: YBWL101498. Outdoor use. Refrigerant: R-22. Test pressure (hi/lo): 450/300 psig. Power supply: 460 V, 60 Hz, 3 phase. Minimum circuit ampacity: 202 amps. Max. dual element fuse size: 225 amps. Maximum circuit breaker size: 225 amps. (2) Copeland 8-Cylinder Reciprocating Compressors, Models: 8DP2-5000FSD and 8DP15000FSD, S/N's: 11516 and 11104, power supply: 460 V, 80 RLA, 510 LRA. (2) Condenser Fans, 5 hp, power supply: 460 V, 7.1 FLA, 41.8 LRA. Electronic Controls, power supply: 115 V, 60 Hz, single phase. (2) Oil Heaters, power supply: 115 V, 60 Hz, single phase, 100 watts (ea). Cooler heater, power supply: 115 V, 60 Hz, single phase. Inlets/outlets: (2) 4 in. dia. ports. Overall dimensions: 9 ft. 7 in. L x 8 ft. W x 7 ft. 10 in. H.







