

## Trane 50 Ton Condensing Unit

Mfg: Trane

Model: RAUCC504BG03ADF1

Stock No. DBPF257.5

Serial No. J93A80138

### Trane 50 Ton Condensing Unit.

- Model RAUCC504BG03ADF1
- S/N J93A80138.
- 460 volts, 60 Hz, 3 phase. Voltage range: 416-508, Nominal Voltages: 440-460-480, Minimum Circuit Amps: 106, Maximum Fuse Size: 125.
- Compressor Motor A: Qty: 1, 460 volts, 60 Hz, 3 phase, RLA: 26.3, LRA: 142.
- Compressor Motor B: Qty: 1, 460 volts, 60 Hz, 3 phase, RLA: 18.1, LRA: 95.
- Compressor Motor C: Qty: 1, 460 volts, 60 Hz, 3 phase, RLA: 26.3, LRA: 142.
- Compressor Motor D: Qty: 1, 460 volts, 60 Hz, 3 phase, RLA: 18.1, LRA: 95.
- Condenser Motor Fan: Qty: 6, 460 volts, 60 Hz, 3 phase, FLA (each): 1.8, HP (each): 1.
- Unit Weight: 3,266, Design Pressure (PSIG): 450, HP: 450, LP: 300.
- Overall Dimensions: 82 in. H x 115 in. L x 89 in. W.





