

Krack Levitor Air Cooled Condensing Unit- 40 Ton

Mfg: Krack

Model: SLD-0400-H2K-133CE

Stock No. DCBJ884B.29

Serial No. 680359-10

Krack Levitor Air Cooled Condensing Unit- 40 Ton. Model: SLD-0400-H2K-133CE. S/N: 680359-10. Outdoor unit. Refrigerant: R-22. Design pressure hi/lo: 400/200 psig. System requirements: 208-230 V, 60 Hz, 3 phase. (3) Fan motors, 1.5 hp, 208-230 V, 18.0 FLA, 60 Hz, 3 phase. Single compressor. Copeland Copelmatic Reciprocating Compressor, Model: 6D53-400 ETSN, S/N: CCD0011772, 6-cylinder, electrical requirements: 230/460-200/400 V, 142/71 RLA, 60/50 Hz, 3 phase. Rated for high temperatures. Inlets: (1) 2-1/8 in. dia. suction. Outlets: (1) 1-1/8 in. dia. discharge. Overall dimensions: 17 ft. 5 in. L x 52 in. W x 59 in. H.

