

1994 Evapco PMCA Series Evaporative Condenser - 715 Tons


Mfg: Evapco

Model: PMCA-715

Stock No: DFDT03

Serial No: 942572M

1994 Evapco PMCA Series Evaporative Condenser. Model: PMCA -715. Serial No: 942572M. Nominal capacity: 715 tons using R-22 with a 105°F condensing temperature, 40°F suction temperature and a 78°F wet bulb temperature, and 500 tons with R-717 with a 96.3°F condensing temperature, 20°F suction temperature, and a 78°F wet bulb temperature. Bell & Gossett pump. Model: 5A6-7/8 BF Serial no. 1792420. U.S. Electrical Motors: 7-1/2 hp, 460V, 60 Hz, 3 phase. Square "D" toggle control. 20 hp fan motor: 460V, 60 Hz, 3 phase. 10 fan motor: 460V, 60 Hz, 3 phase. Configured for left-handed application. Inlets /outlets: (4) 4 in. refrigerant in and out connections, 3 in. overflow and drain, 2 in. make-up. Listed shipping weight: 29030 lbs. Overall dimensions: 21 ft. 9 in. L x 9 ft. 11-3/4 in. W x 14 ft. 7-3/4 in. H.









evapco

EVAPCO, INC. -Midwest Plant
 York Road Greenup, Illinois 62428
 (217) 923-3431

MFG. UNDER ONE OR MORE OF THE FOLLOWING U.S. PATENTS:
 4500330, 4579694, 4755331, 5124087 MADE IN U.S.A.

MODEL NO.	PMCA-715	SERIAL NO.	942572M
BELT NO.	2B133	1267	COIL TEST PRESSURE 300 P.S.I.G.

FOR EVAPCO AUTHORIZED PARTS AND SERVICE, CONTACT MR. GOODTOWE

WILD BELL & ASSOCIATES
 2340 N.W. MacArthur Highway, Suite 100
 Dallas, Texas 75243
 Phone: (214) 520-0270

Mr. GoodTowe

Featuring the 

Thermal-Pak Coil™

US PATENT NO. 4,758,331

ENCLOSED HIGH EFFICIENCY UNMOUNT

HP	2.5	PH : HZ 60	RPM	1725	CODE - NEMA DESIGN B
FRAME	56C	1/4	ST	1.0	MAX AMPS 40%
VOLTS	208	208	208	CHART	END BRG.
1.1 AMP	25.0	12.5		OPP	

USABLE ON 3001 AT 22.5 AMPS OR 180/187 4 8/10

U.S. ELECTRICAL MOTORS
 DIVISION OF EMERSON ELECTRIC CO.
 MILFORD, CONNECTICUT

STAR-Y CONNECTION

BELL & GOSWORTHY

1531 PUMP

MAX. W.P.	175 P.S.I.	MODEL NO.	5A 6-7/8 BF
		SERIAL NO.	1792420
GPM	75	FT	75

FLUIDS: MORTON