

1999 Frick Rotary Screw Compressor Package- 400 HP

Mfg: Frick

Model: RWF 222 E

Stock No. DMNY004.

Serial No. S0008UFMNTAC03

1999 Frick Rotary Screw Compressor Package- 400 HP. Model: RWF 222 E. S/N:S0008UFMNTAC03. Refrigerant: R-717. Maximum design pressure: 300 psig. Frick Compressor, Model: SHC2317011, volume ratio: 22-50, maximum speed: 4500 rpm. Ram Motor, 40 hp, 3570 rpm, 460 V, 440 FLA, 60 Hz, 3 phase. Frick Oil Separator, Nat'l Bd: 141545, MAWP @ 250 °F: 300/FV psi, MDMT @ 300/FV psi: -20 °F. Frick Oil Cooler, Nat'l Bd: 141661, MAWP @ 250 °F: 400/FV psi, MDMT @ 400/FV psi: -20 °F. Equipped with Frick Volumizer Ratio Control feature and Frick/York Int'l. controls, electrical requirements: 115 VAC. Inlets: (1) 5-1/2 in. dia. suction port. Outlets: (1) 4 in. dia. discharge. Overall dimensions: 10 ft. L x 45 in. W x 85 in. H.







