

**Reco / Frick RWB-100 Rotary Screw Compressor Package – 250 HP**

**Mfg: Reco / Frick**

**Model: GDSH193S0081P / RWB-100**

**Stock No: DPFI435.3**

**Serial No: GDSH193S0081P**

Reco / Frick RWB-100 Rotary Screw Compressor Package. Same machine as FRICK RWB-100. Model: GDSH193S0081P / RWB-100. S/N: GDSH193S0081P. Refrigerant: last used with R-717 (ammonia). Variable Vi setting: 2.2-5.0. Displacement: 592 cfm. Max speed: 4,500 rpm. MAWP: 362 psig (2,500kPA). General Electric motor, 250 hp, 3,550 rpm, 460 V, 280 FLA, 60 cycles, 3 phase. Inlets: (1) 6 in. suction pipe. Outlets: (1) 3 in. dia. discharge pipe, (1) 3-1/2 in. discharge pipe. Reco oil separator, S/N: M852230-A, MAWP 250 psi at -20 to 300 °F. Reco oil cooler, S/N: M906060G, shell side MAWP @ 300 °F: 350 psi., tube side MAWP @ 300 °F: 250 psi., shell side MDMT @ 350 psi: -20 °F, tube side MDMT @ 250 psi: -20 °F. (2) Henry Technologies pressure relief valves, Cat No: 5604, set psi: 250, capacity 116.1 lbs air/min. (2) Hansen Technologies pressure relief valves, Cat No: H5622A, set pressure: 250 psi. Overall dimensions: 11 ft. 2 in. L x 6 ft. 2 in. W x 7 ft. 10 in. H.









