

Frick/York Rotary Screw Compressor

Mfg: Frick/York

Model: RXB-50

Stock No. DPF1805.4a

Serial No. S0189MFMNLHAA3

Frick/York Rotary Screw Compressor. Model: RXB-50. S/N: S0189MFMNLHAA3. Refrigerant: R-77/R-22. Compressor run time: 81233 hrs. Ram Motor, 125 hp, 3540 rpm, 230/460 V, 294/147 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. suction pipe. Outlets: (1) 3 in. dia. discharge pipe. Overall dimensions: 9 ft. L x 55 in. W x 60 in. H.

Frick Oil Cooler, S/N: MC93103. MAWP @ 200 °F: 300 psi., MDMT @ 10.2 psig: -20 °F. Frick Oil Separator, S/N: 109719, MAWP @ 200 °F: 300 psi, MDMT @ 10.2 psig: -20 °F. RXB Plus Control Panel with touchpad controls and digital display. Starter included.



