

Frick/York Screw Compressor Unit-100 hp

Mfg: Frick/York

Model: RWB II 38 H

Stock No. DPF1807.8a

Serial No. S0007CFMPLHAC3

Frick/York Screw Compressor Unit-100 hp. Model: RWB II 38 H. S/N: S0007CFMPLHAC3. Refrigerant: R-717. Volume ratio: 22-50. MAWP: 300 psig. Compressor run time: 19144 hrs. Westinghouse Motor, 100 hp, 1770 rpm, 230/460 V, 230/115 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. suction pipe. Outlets: (1) 3-1/2 in. dia. discharge pipe. Overall dimensions: 90 in. L x 50 in. W x 73 in. H.

2003 Frick Rotary Screw Compressor, Model: TDSH163L2163B, refrigerant: R-717, max speed: 4500 rpm, MAWP: 350 psig. 1990 Frick Oil Cooler, Nat'l Bd: 91089, MAWP at 200 °F: 300 psi., MDMT at 10.2 psig: -20 °F. 1997 Frick Oil Separator, S/N: 56742, MAWP at 200 °F: 300 psi., shell thickness: .187, head thickness: .187, ellip: 2/1. 1996 Frick RWB II Plus Control Panel, touchpad controls with digital display, electrical requirements: 115 VAC, 5 amps, 50/60 Hz. Starter included.



