

## Frick RWB II 38 Rotary Screw Compressor Package - 100 hp

Mfg: Frick

Model: RWB-II-38 H

Stock No: DPFI808.8a

Serial No: S0008CFMPLHAC3

Frick RWB II 38 Rotary Screw Compressor Package. Model: RWB-II-38 H. S/N: S0008CFMPLHAC3. Sales Order No: 261164-01. Frick rotary screw compressor, Model/Serial: TDSH163L1840B. Refrigerant: Last used with R-717 (ammonia). Variable Vi setting: 2.2 – 5.0. Displacement: 224 cfm. Max speed: 1,800 rpm. MAWP: 300 psig. Frick oil separator. Frick coalescer vessel, Nat'l Bd. No: 136926, MAWP: 300 psi at 200°F and -20°F. Westinghouse electric motor, 100 hp, 1,770 rpm, 230/460 V, 230/115 amps, 60 Hz, 3 phase. Frick RWBII Plus control panel. Inlets: (1) 4 in. dia. suction pipe. Outlets: (1) 3-1/2 in. dia. discharge pipe. Compressor run time: 15,958 hrs. Overall dimensions: 7 ft. 6 in. L x 4 ft. 2 in. W x 6 ft. 1 in. H.







