

Conair Thermulator Water-Cooled Chiller- 40 Ton

Mfg: Conair

Model: CLCW-40

Stock No. DRGP071B.

Serial No. 38016

Conair Thermulator Water-Cooled Chiller- 40 Ton. Model: CLCW-40. S/N: 38016. Dwg: 102E76-1. Refrigerant: R-22. MAWP @ 65 °F: 100 psi. Test pressure: 300 psi. System requirements: 460 V, 102.3 amps, 60 Hz, 3 phase. Control voltage: 115 V. (2) Compressor Products Inc. 4-Cylinder Reciprocating Compressors, Models: 4RK12500T-SK and 4RK2-2500TS-J. S/N's: 10744 and 9863, 200-230/460 V. Inlets: (1) 2 in. dia. PVC pipe (chiller barrel), (1) 2 in. dia. PVC pipe (condenser). Outlets: (1) 2 in. dia. PVC pipe (chiller barrel), (1) 2 in. dia. PVC pipe (condenser). Overall dimensions: 11 ft. 4 in. L x 54 in. W x 9 ft. 1 in.

1993 Ketama Shell and Tube Condenser, S/N's: M934367C5 and M934367C6, shell side MAWP @ 250 °F: 350 psi, shell side MDMT @ 350 psi: -20 °F, tube side MAWP @ 150 °F: 150 psi, tube side MDMT @ 150 psi: -20 °F.



