

Frigomeccanica Programme Industrial Refrigerated Water Chiller- 4 Ton

Mfg: Frigomeccanica Programme

Model: MK

Stock No. DSVT020.11a

Serial No.:

Frigomeccanica Programme Industrial Refrigerated Chiller- 4 Ton. Model: MK. Matriculate: 13783. Refrigerant: R-22. Air cooled. Motor pump: 1.47 hp (1.1Kw), 3480 rpm (3480 1/min), 277/248 V, 5/2.9 amps, 60 Hz. Pump, Type: NM 25/160 BE, H maximum 31 cu. m/hr & m-Q minimum 3 cu. m/hr, H minimum 20 cu m/hr & m-Q maximum 10.8 cu m/hr. Evaporator Panel, dimensions: 55 in. L x 36 in. W. Chiller dimensions: 18-1/2 in. diameter x 55-1/2 in. L. Gruppo Industrial Ercole Marrelli Fan motor, matricula: MA 9084B3. Fan dimensions: 16 in. diameter x 18-1/2 in. L, outlet air aperture: 18 in. L x 15 in. W. Oil container dimensions: 11-1/2 in. diameter x 13 in. H. Control panel: pump switch, compressor switch. Chiller pipe components: low pressure switch, high pressure switch, water gauge: 0-100 mH2O. Inlets/outlets: 2-1/2 in. threaded female, 2-1/2 in. threaded male. Overall dimensions: 85 in. L x 45 in. W x 67 in. H.

Fan motor capacities:

Hz	Kw	V	Amps	1/min
50	1.1	220/380	4.85/2.8	1390
50	1.1	240/415	5.2/3.0	1410
60	1.32	277/480	4.85/2.8	1670





