

## Stainless Steel Single Shell Vertical Silo- 7,000 Gallon

|                            |                    |
|----------------------------|--------------------|
| <b>Mfg:</b>                | <b>Model:</b>      |
| <b>Stock No. DTTC2014.</b> | <b>Serial No.:</b> |

Stainless Steel Single Shell Vertical Silo- 7,000 Gallon. Inside straight-wall dimensions: 8 ft. dia. x 18 ft. 6 in. H. CIP sprayball. Rosemount Pressure Transmitter. (2) Level indicator probes. (1) Thermocouple. 18 in. dia. manway with internal step ladder. Inlets: (1) 2-1/2 in. dia. port (CIP sprayball), (1) 4 in. dia. 150lb ANSI flanged port. Outlets: (2) 2-1/2 in. dia. 150lb ANSI flanged ports with butterfly valves, (2) 4 in. dia. 150lb ANSI flanged ports with butterfly valves, (2) 4 in. dia. ACME fitting with butterfly valves, (1) 6 in. dia. 150lb ANSI flanged port with butterfly valve. Originally installed at PepsiCo. / Tropicana and used in orange juice production, these silos have side agitators and slight slopes to their drains. Overall dimensions: 9 ft. 4 in. L x 8 ft. 6 in. W x 21 ft. H.



