

1997 Frick Screw Compressor Package-800 HP

Mfg: Frick

Model: RWBII316-H

Stock No. DTTC828.

Serial No. SO377RFMPLTAA00

1997 Frick Screw Compressor Package-800 HP. Model: RWBII316-H. S/N: SO377RFMPLTAA00. Refrigerant: R-717. Volume ratio: 2.2/5.0. Maximum speed: 6600 rpm, Design pressure: 650 psig. Capacity: 668 TR. Louis Allis Motor, Type: DPX, S/N: 8RMM344L, 800 hp, 3560 rpm, 2300/4000 V, 182/105 amps, 60 Hz, 3 phase. Oil Separator, Natd Bd and S/N: 136634, shell chamber MAWP: 300 psi @ 200 °F, MDMT: -20 °F @ 300 psi, maximum design pressure: 300 psig. Viking Rotary Pump, Model: HU2954, S/N: 10873704. US Unimount Motor, 1.5 hp, 208-230/460 V, 5.1-5.0/2.5 amps, 1730 rpm, 60 Hz, 3 phase. Outlets: (1) 6 in. dia. discharge. Overall dimensions: 16 ft. 3 in. L x 72 in. W x 93 in. H. (SR500).









