

Evapco Evaporative Condenser – 920 Ton

Mfg: Evapco

Model: PMC-920N

Stock No.: DTTC851

Serial No.: 879222RH

Evapco Evaporative Condenser – 920 Ton. Model: PMC920N. S/N: 879222RH. Nominal capacity: 920 Tons of R-22 at 105°F condensing temperature, 40°F suction temperature, and 78°F wet bulb temperature. R-717 (ammonia) capacity rating: 653 tons of at 96.3°F condensing temperature, 20°F suction temperature and 78°F wet bulb temperature. (2) 7-1/2 hp and (2) 5 hp, 230-460/60/3 fan motors. (2) 5 hp, 230-460/60/3 water pumps. Stainless steel mist eliminators. Shipping weight: 50,760 lbs. Operating weight: 55,020 lbs. Overall dimensions: 39 ft. 1 in. L x 9 ft. 11-3/4 in. W x 13 ft. 9-1/2 in. H. (ACN1011-87).



