

Evapco PMCA-Series Evaporative Condenser- 625 Tons

Mfg: Evapco

Model: PMCA-625

Stock No: DTTC864

Serial No: 870118

Evapco PMCA-Series Evaporative Condenser. Model: PMCA-625. S/N: 870118. Belt: 2B-128. Rated capacities: 625 tons using R-22 at 105°F condensing, 40°F suction and 78°F wet bulb temperatures, or 450 tons using R-717 at 96.3°F condensing, 20°F suction and 78°F wet bulb temperatures. Coil test pressure: 350 psig. (3) 60 in. dia. fans. U.S. Motor, 10 hp, 1760 rpm, 230/460 V, 24.6/21.3 amps, 60 Hz, 3 phase. Motor, 20 hp, 230/460 V, 60 Hz, 3 phase. (2) manways: 1 ft. 8 in. dia. Inlet: (1) 4 in. dia. port, (1) 6 in. dia. port. Outlets: (2) 4 in. dia. port, (3) 2 in. dia. ports, (1) 6 in. flanged port. Overall dimensions: 19 ft. 8 in. x 9 ft. 8 in. x 13 ft. 3 in. H.(ACN880-87).





