

Belding Tank Technologies Stapco Perma San Dimple Jacketed Vertical Tank - 1400 Gallon

Mfg: Perma San

Model: 1400 gallon JCVC

Stock No. DTWA397.40

Serial No. 43702-2

Belding Tank Technologies Stapco Perma San Dimple Jacketed Vertical Tank-1400 Gallon. Model: 1400 gallon JCVC. S/N: 43702-2. National Board: 4900. 304 Stainless steel construction. Full jacketing on sides and bottom. Jacket: 50 psi at 300 °F. Shell: 0.103, head thickness: 0.110. Crown radius: 84 in. Domed, ASME, 4+deep bottom. Inside dimensions: 56 in. Dia. x 11 ft. H. Siemens Allis agitator motor: 5 hp, 1745 rpm, 230/460 V, 13.44/6.72 amps, 60 Hz, 3 phase. Eurodrive gear motor, input max: 1750 rpm, final rpm: 43. Flange-mounted agitator, shaft: 150 in. L x 2-1/2 in. diameter, (3) propellers: 36 in. L. (2) Spray ball system, manway: 18 in. diameter, temperature gauge. Product inlet: 3 in. threaded (female), spray ball inlet: 2 in. treaded (male), jacket inlet: 1 in. threaded (female) outlet: 2 in. threaded (male). Overall dimensions: 65 in. diameter x 15 ft. H.



