

## Heatcraft Inc Climate Control Air Cooled Condensing Unit- 4.4 Ton

Mfg: Heatcraft Inc.

Model:

Stock No.: DWKN206.3

Serial No.:

Climate Control Air Cooled Condensing Unit- 4.4 Ton. Copeland 2-Cylinder Reciprocating Compressor, Model: 2DL3-0750-TDF, S/N: CT 90J 03169 S, B/M: 211, capacity (medium temperature): 52,800 Btuh, power supply: 380-420/460 V, 13.8 RLA, 8.5 LRA, 50/60 Hz, 3 phase. Number of fans: 2. Fan diameter: 2 ft. (2) Emmerson Motors, 3/4 hp, 1080 rpm, 460 V, 2.1 amps, 60 Hz, single phase. Evaporator, fins per inch: 12 fpi. Receiver- 10 Gallon, inside straight-wall dimensions: 8 in. dia. x 4 ft. L. Cutler Hammer Heavy Duty Safety Switch, power supply: 600 VAC, 30 amps. Inlets: (1) 1 in. dia. compressor suction port. Outlets: (1) 1/2 in. dia. compressor discharge port. Overall dimensions: 5 ft. 7 in. L x 4 ft. 3-1/2 in. W x 3 ft. 8 in. H.







