

## New Un-used APV Crepaco Amerio Manual Contact Plate Freezer

Mfg: APV Crepaco

Model: 12

Stock No: DWKN207.60

Serial No: G-6368

New Un-Used APV Crepaco Amerio Manual Contact Plate Freezer. Model: 12. S/N: G-6368. Refrigerant: R-22. Number of plates: 7. Number of stations: 6. Plate material: extended aluminum. Plate dimensions: 3 ft. 9 in. L x 2 ft. W. Plate thickness: 1 in. Maximum aperture between plates: 4-1/2 in., minimum aperture between plates: 1 in. Approximate capacity rating on hamburger patties: 215 lbs./hr. based on 1/4 inch thick patties, 1/4 lbs. each, going from a starting temperature of 40°F to a core temperature of 0°F, where plate temperature is -45°F and approximately 3 tons of refrigeration is used. Leer Manufacturing Company Commercial Walk-In Cooler/Freezer: Model: DS5232FRN. S/N: 371480CRP-92W. Inside straight-wall dimensions: 4 ft. 4 in. L x 3 ft. 5 in. W x 2 ft. 9 in. H. Dunham-Bush reciprocating compressor: Model: DB41VSM, S/N: 71701501A92C. Design pressure (hi/lo): 400/150 psig. Power supply: 460 V, 9.2 amps. Suction accumulator tank (2.5 Gallon), inside straight-wall dimensions: 6 in. dia. x 1 ft. 9 in. L. Leeson Electric Motor: 7-1/2 hp, 1750 rpm, 208-230/460 V, 20-18.4/9.2 amps, 60 Hz, 3 phase. Hydraulic pump with Reliance electric motor: 1/4 hp, 1725 rpm, 120V, 5.2 amps, 60 Hz, single phase. Self-contained, hydraulic system with hydraulic cylinder and manual operating valve. Cylinder bore: 3-1/4 in. Cylinder stroke: 16-1/2 in. Inlets/outlets: 4 ft. 4 in. W x 2 ft. 9 in. H. Overall dimensions: 5 ft. 2 in. L x 3 ft. 8 in. W x 9 ft. H. (ACN254).

















