

Feldmeier Triple Tube Single Stage Pasteurizer

Mfg: Genemco, Inc.

Model:

Stock No: GEN1101

Serial No:

Feldmeier Triple Tube Single Stage Pasteurizer. (24) concentrically mounted tubes with the following conformation: thickness: 0.060 in. Inner tube: 1.38 in. diameter (inner dia.) x 240 in. L, total holding capacity: 38.5 gal. Intermediate tube: 1.88 in. diameter (inner dia.) x 235 in. L, total holding capacity: 29 gal. Outer tube: 2.38 in. diameter (inner dia.) x 220 in. L, total holding capacity: 33 gal. Skid features: a SSP Pumps Ltd. positive displacement pump, model: SK/3/038/LD, serial no: 950094/01B with a volume displacement capacity rating of 8.36 gal./100 revolutions and an approximate current capacity of 22.57 gpm. This pump package features a stainless steel rotor, Brook Crompton electric motor, 4 hp, 1420 rpm, 415 V, 6.5 amps, 50 Hz, 3 phase, Opperman Mastergear drive, ratio: 5.262, rpm in/out: 1420/270 (final). Inlets/outlets: (2) 2" dia. S-Line fittings. Also featured is a Schweitzer's single shell stainless steel balance tank no. 8248-90 with a listed, 85 gallon capacity. Inside dimensions: 2 ft. 11 in. dia. x 1 ft. 8-1/2 in. straight wall. Inlets: (4) 2-1/2 in. s-line. (1) 2-1/2 in. acme. (1) 2 in. acme. (1) 4-5/8 in. port. Outlets: (1) 2-1/2 in. acme. (1) 2 in. acme. Finally, included is a hot water set with a Bell and Gossett SU-45-2 heat exchanger and a Carver centrifugal pump, type 2.5x2x7LA-33D. Overall dimensions: 21 ft. L x 5 ft. 2 in. W x 7 ft. 8 in. H











