

Cherry Burrell Cone Bottom Pressure Wall Processor-100 Gallon

Mfg: Cherry Burrell

Model:

Stock No. 79a.GR669.

Serial No. 81-E-99

Cherry Burrell Cone Bottom Pressure Wall Processor-100 Gallon. S/N 81-E-99. Jacket rating 125 psi at 250° F, 2 in. jacket thickness, jacket connections 1-1/2 in., tank outlet 2 in. close coupled ball outlet with clamp connection, center bridge with lift top covers, lightning agitator, Model NLDG-33VM, S/N 81/100589, 1/3 hp 90 V, DC 1,725 rpm, 3-blade propeller 9 in. spread, 2 vertical baffles 4 in. W x 24 in. H. Legs 15 in. H, inner dimensions: 41-1/2 in. dia. x 34 in. H, Overall dimensions 52 in. dia. x 71 in. H.

