



NOTES:

1. (M) - FAN MOTOR LOCATION
2. MAKE-UP WATER PRESSURE 20psi MIN. 50psi MAX.
3. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
4. HEAVIEST SECTION IS COIL SECTION
5. ALL NIPPLE LOCATIONS ARE APPROXIMATE DIMENSIONS. DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
6. MPT DENOTES MALE PIPE THREAD.
7. FPT DENOTES FEMALE PIPE THREAD.

WEIGHTS			NO. SHIPPING SECTIONS
SHIPPING	OPER.	HEAVIEST SECTION	
15250	21100	10740	2

MODEL NUMBER (1) PMCB-330 Evaporator Condenser
 CERTIFIED FOR Cumberland Farms, Inc. TAG _____
 CUSTOMER ORDER NO. R157826 EVAPCO NO. 961170
 CAPACITY 234 TR R-717 REFRIG. 96.3 °COND +20 °SUCT 78 °W.B.
 FAN MOTOR (1) 7.5 H.P. ELEC. SPEC. 460/60/3
 PUMP MOTOR (1) 5 H.P. ELEC. SPEC. 460/60/3
 REMARKS Drives sized for 0" ESP.
{ Unit to be supplied with bottom remote sump outlet connection, for future use.



**EVAPORATIVE
CONDENSER**

REV TAS DATE 6/20/96

CP101208ERB-12