

## 1996 Evapco PMCB Series Evaporative Condenser—330 Nominal Tons

Mfg: Evapco

Model: PMCB-330

Stock No. HDCF215.79

Serial No. 961170

1996 Evapco PMCB Series Evaporative Condenser. 330 Nominal Tons. Model: PMCB-330. S/N: 961170. Refrigerant: R-717. TR is 234 at 96.3°F condensing, 20° suction with at 78°F wet bulb. Belt No: 2B-133. Coil test pressure: 350 psig. (1) fan, diameter: 60 in. WEG Motor, 7.5/7.1 hp, 1765/1445 rpm, 208-230/460-380 V, 19.1/9.53-12.1 amps, 60/50 Hz, 3 phase. Scot Motorpump, Model: 58, impeller diameter: 5.50 in. U.S. Motor, 5.00/4.70 hp, 1745 rpm, 208-230/460-190/380 V, 15.00-13.70/6.85-15.30/7.65 amps, 60/50 Hz, 3 phase. Inlets: (2) 4 in. dia. refrigerant ports. Outlets: (2) 4 in. dia. refrigerant ports, (1) 3 in. dia. NPT (drain), (1) 3 in. dia. FNPT (overflow). Overall dimensions: 13 ft. 3 in. L x 10 ft. W x 13 ft. 3-1/2 in. H.







Note: the following pictures show the exact unit prior to removal.

