

Cherry Burrell Horizontal Refrigerated Tank- 3000 Gallon

Mfg: Cherry Burrell

Model: GHW

Stock No. HDPW705.17a

Serial No. 50-64-205

Cherry Burrell Horizontal Refrigerated Tank- 3000 Gallon. Model: GHW. S/N: 50-64-205. Stainless steel interior. Percent coldwall: 25%. Refrigerant: full-flooded ammonia. CIP sprayball for CIP cleaning. Manway: 20 in. W x 16 in. H. Master AC Multispeed Motor, .75/.37 hp, 1725/860 rpm, 72/36 rpm (final), 220 V, 2.2/1.6 amps, 60 Hz, 3 phase. Inlets: 3 in. dia. NPT (male). Outlet: (1) 2-1/2 in. Overall dimensions: 12 ft. 8 in. L x 8 ft. 6 in. W x 10 ft. 2 in. H.



