

1998 Evapco PMCB Series Evaporative Condenser

Mfg: Evapco

Model: PMCB 390

Stock No. pHDRG214.86

Serial No. 988297W

1998 Evapco PMCB Series Evaporative Condenser. Model: PMCB 390. S/N: 988297W. Belt No: 2B133. Centrifugal Pump. Impeller diameter: 5-1/2 in. U.S. Electric Motor, 5 hp, 1745 rpm, 208-230/460 V, 15-13.6/6.8 amps, 60 Hz, 3 phase. Fan diameter: 5 ft. U.S. Electric Motor, 15 hp, 1775/1460 rpm, 208-230/460-190/380 V, 40.0-37.0/18.5-46.0/22.5 amps, 60/50 Hz, 3 phase. Driver pulley diameter: 6 in. dia. Driven pulley diameter: 1 ft. 7 in. Pulley ratio: 0.32. Final fan speed: 560.5 rpm. Inlets: (2) 4 in. dia. ports. Outlets: (1) 1-1/2 in. dia. port, (2) 4 in. dia. ports, (1) 2 in. dia. port, (1) 2-1/2 in. dia. port. Overall dimensions: 15 ft. 2 in. L x 10 ft. 10 in. W x 16 ft. 1 in. H.











3255K030 891152 F98
 MOTORPUMP 58 STANDARD FITTED
 5 X 4 BN-CM SEAL
 5.50 IMP DIAMETER
 5 HP TEFC 1750 RPM
 3/60/230/460V

 EVAPCO WEST, MADERA, CA
 209-673-2207 FAX 209-673-2378

ENCLOSED HIGH EFFICIENCY MOTOR
 MODEL 8075A HP 5.0 PH 3 HZ 60 RPM 1745 DES B
 FRAME 184JM TYPE U14 ENCL TE SF 1.25 CODE J INHL CLASS F
 VOLTS 208-230/460 MAX AMB 40 °C DUTY CONT BEHA NOM EFFICIENCY 85.5
 FL AMPS 15.0-13 6/6.8 SHFT END BRG 6307-22-J/C3
 SF AMPS 16.6/8.3 OPP END BRG 6205-22-J/C3
 ID# 8075-803-4918-M 4.7 HP@50HZ SF. 1.0

 USABLE ON 208V 60HZ ALTERNATE 15.8/7.9 AMPS MAX AT 190/380V 50HZ
 AT 1.6/2.2 AMPS MAX RATINGS 40°C AMB 1.25 SF CLASS B
 50°C AMB 1.75 SF CLASS F
 U.S. ELECTRICAL MOTORS
 DIVISION OF EMERSON ELECTRIC CO.
 ST. LOUIS, MO
 MADE IN MEXICO 391841-732
 I 1 2 3 4 Y 0 1 2 3 4
 N 1 2 3 4 N 1 2 3 4
 H VOLT N L0 VOLT