

## Perma-San Pressure Wall Jacketed Processor Tank-1000 Gallon

Mfg: Perma-San

Model: JOVS

Stock No. HEC004.

Serial No. 38263

Perma-San Pressure Wall Jacketed Processor Tank-1000 Gallon. Model JOVS, S/N 38263. Nat'l Bd: 4306. 316 stainless steel. 2-piece removable top cover. Slope bottom. Prop-style mixer mounted on mild steel bridge. Water jacket (side and bottom) rated for 85 psi @ 333°F. Shell and head thickness: 0.134 in. Adjustable mild steel legs with ball feet. Lightnin Mixer, Model: NLDO-100. Pacemaker Motor, 3 hp, 1740 rpm, 230/460 V, 9.2/4.6 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. threaded jacket inlet, (1) 3/4 in. dia. thermowell. Outlets: (1) 1-1/2 in. dia. threaded from jacket, (1) 2 in. dia. threaded from tank. Overall dimensions: 75 in. L x 72 in. W x 10 ft. 3 in. H.



