

**Dome-Top Sloped Bottom Jacketed Mix Tank-350 Gallon**

**Mfg:**

**Model:**

**Stock No. JMB525**

**Serial No.**

Dome-Top Sloped Bottom Jacketed Mix Tank-350 Gallon. Set up for use with steam, agitator blades 23 in. W, motor 5 hp, 230/460 V, 1,745 rpm, motor pulley diameter 4 in., gear pulley diameter 9 in., ratio 30, 57.8 final rpm, 1 in. jacket outlet, 2.5 in. side outlet, 9 in. x 3 in. bottom outlet, top jacket insulated inlet 2 in. ID 6 in. insulated OD, 2 in. ferruled top inlet, 30 in. W x 29 in. L x 19 in. H, top square opening, 5 in. sight glass, overall 81 in. H x 81 in. W.

