

Frick RWB-II-100 Booster Compressor Package – 75 HP

Mfg: Frick

Model: RWB II 100B

Stock No.: KRKS01

Serial No.: S0141FFMFLHAA3

Frick Rotary Screw Booster Compressor Package. Model: RWB-II-100-B. Serial: S0141FFMFLHAA3. Sales order: 262109-02. Refrigerant: R717 (ammonia). Screw compressor model: TDSH193S3026CR. Volume ratio: 2.2-5.0. Year: 2008. Frick Quantum LX retrofit micro controller panel. Frick oil separator vessel: MAWP: 300 PSIG, year 1987. Toshiba High Efficiency Induction Motor: 75 HP, 3520 RPM, 240/480V, 168/84 amps, 3-phase, 60 Hz, 364TS frame.





Frick
 ROTARY SCREW
 COMPRESSOR UNIT

UNIT MODEL NO.	300 II 300 D
UNIT SER. NO.	50141FFMFLPAA3
FRICK SALES ORD.	252109-02
REFRIGERANT	R717
MAX. SPEED RPM	3600
MAX. DESIGN PRESSURE PSIG	300
MAX. DESIGN PRESSURE kPa	2068

WAYNESBORO, PA. 17268

Frick
 ROTARY SCREW COMPRESSOR
 MODEL/SERIAL NO.

TDSIH098S3026CR

REFRIGERANT	R717
VOLUME RATIO	2.2-5.0
MAX DRIVER SPEED RPM	4500
SWEPT VOLUME FT ³ /MIN @ MAX SPEED	7.00
MAX ALLOWABLE PRESSURE PSIG	400
YEAR OF MFR	2008

COMPRESSOR AND MOTOR PATENTS LICENSED FROM SWEDISH PATENT MARIENB. 562102481, SWEDEN
 WAYNESBORO, PA. 17268



