

Reco - Evapco Evaporative Condenser – 355 Tons

Mfg: Reco-Evapco

Model: RA522N

Stock No: KWBF002

Serial No: 879486

Reco - Evapco Evaporative Condenser. Model: RA522N. Serial No: 879486. Nominal capacity: 355 tons using R-22 with a 105°F condensing temperature, 40°F suction temperature and a 78°F wet bulb temperature, and 252 tons with R-717 with a 96.3°F condensing temperature, 20°F suction temperature, and a 78°F wet bulb temperature. (2) Axial fans, 5 ft. diameter. Fan displacement: 63,800 cfm. (1) Magnetek fan motor, 15 hp, 1755 rpm, 230/460V. Evapco pump, impeller diameter: 5.88 in. Baldor pump motor, 3 HP, 1750 rpm, 208-230/460 V. Inlets: (2) 1 ft. 8 in. man ways, (2) 4 in. dia. port, (1) 3 in. dia. port, (1) 2 in. dia. port. Outlets: (3) 4 in. dia. port, (1) 3 in. dia. port, (1) 2 in dia. port. Overall dimensions: 13 ft. 3 in. L x 10 ft. Wx13 ft 7 in. H.(ACN430).





