

## Carrier Chiller Model 30GB075650

**Mfg: Carrier**

**Model: 30GB075650**

**Stock No. LEPH01.**

**Serial No. T698196**

Carrier Chiller. Model 30GB075650, S/N T698196. Mfg Date: 6-86. Min Circuit Amps: 187.3, Max Overcurrent Protective Device: 225 fuse only. Control Power Supply: 115 Volts Phase: 1 Hz: 60 Amps: 20.

	<u>Qty</u>	<u>Volts</u>	<u>Phase</u>	<u>Hz</u>	<u>RLA</u>	<u>LRA</u>	<u>Refrig-R22</u>	(Factory charged)
Compressor 1:		2	460	3	60	52.1	253	122 lbs
Compressor 2 :	1	460	3	60	52.1	253	70 lbs	

	<u>Design/Test Pressure</u>	
High:	450 psi	3103 kpa
Low:	235 psi	1620 kpa

<u>Fan Motors:</u>	<u>Qty</u>	<u>Volts</u>	<u>Phase</u>	<u>Hz</u>	<u>FLA</u>	<u>HP</u>	<u>KW out</u>
	6	460	3	60	3	1.75 NEC	1.31

<u>Heaters:</u>	<u>Volts</u>	<u>Phase</u>	<u>Hz</u>	permissible voltage at unit:
	460	3	60	508 max 414 min



