

## Carrier Chiller Model 30GB075650

**Mfg: Carrier**

**Model: 30GB075650**

**Stock No. LEPH02.**

**Serial No. T698194**

Carrier Chiller. Model 30GB075650. S/N T698194. Min Circuit Amps: 187.3, Max Overcurrent Protective Device 225 fuse only. Control Power Supply: 115 V, 1 Phase, 60 Hz, 20 Amps.

(factory  
Refrig-R22 charged)

	Qty	Volts	Phase	Hz	RLA	LRA	Refrig-R22	charged)
Compressor 1:	2	460	3	60	60	52.1	253	122 lbs
Compressor 2 :	1	460	3	60	52.1	253	70 lbs	

### Design/Test Pressure

High:	450 psi	3103 kpa
Low:	235 psi	1620 kpa

<u>Fan Motors:</u>	Qty	Volts	Phase	Hz	FLA	HP	KW out
	6	460	3	60	3	1.75 NEC	1.31

<u>Heaters:</u>	Volts	Phase	Hz	permissible voltage at unit:
	460	3	60	508 max 414 min



